NP-ACSMM

Matched Pair Acetylene Pellistor Gas Sensor

DS3350 rev.1 dated 06/10/2021



Key Features

The N.E.T. NP-ACSMM is a catalytic (pellistor) type flammable gas sensor supplied as a matched pair of elements mounted on TO4 size headers and protected by a metal can. The matched pair sensor is mounted in a plastic housing of standard diameter of 32 mm (see

The sensor detects and measures the presence of flammable gases and vapours in air, in the range 0-100% of the Lower Explosive Limit (LEL) of the gas or vapour being measured. Designed as a sensing platform for use in fixed flammable gas detection systems, the NP-ACSMM exhibits excellent long term zero and sensitivity stability and a high level of resistance to catalytic poisons. The device is compatible with a wide range of commercially available Gas Detection Systems and remote flammable gas detection heads.

The highly automated manufacturing procedure employed results in a

NET Catalytic Bead Pellistors

Our Pellistor, or catalytic bead sensor, line is selected by Heads. This will allow the beads to be exposed to the target N.E.T. and manufactured, on OEM basis, by world's best gas without the risk of ignition. manufacturers.

The sensor monitors the presence of a combustible gas or monitor Methane (CH4) and other Hydrocarbons and, genvapor in air (or atmospheres containing oxygen) up to the Lower Explosive Limit (LEL). A Pellistor operates on the principle that when a combustible gas/air mixture is in contact with the catalyst surface, maintained at about 500°C as current is passed through it in a Platinum coil, combustion tion, Pellistors cannot be used in inert atmosoccurs. The heat generated increases the temperature of the bead, which in turn changes the resistance of the coil. The resistive signal change produced is proportional to the gas concentration and can be measured by using the coil as a temperature thermometer in a standard Wheatstone bridge circuit.


certified flameproof enclosure, such as N.E.T. Certified mote flammable gas detector heads.

Pellistors are an inexpensive and effective solution to erally, combustible gases such as Hydrogen (H2) and Ammonia (NH3). They offer very low humidity and temperature dependence.

As their measurement principle is based on combuspheres and require the presence of Oxygen. Additionally, they are susceptible to inhibition and poisoning by chemicals such as Lead- and Sulphur-containing compounds, phosphates and organic silicones. In case any of those two risks are present, try our InfraRed sensors.

The standard dimensions and the electrical output Given Pellistors capacity to ignite flammable gas mix- make our Pellistor perfectly compatible with a wide range tures, is typically necessary to encapsulate the beads in a of commercially available Gas Detection Systems and re-

Mechanical specifications




Product specifications


Technical Specifications	Recommended Voltage:	2.0V +/- 0.1V	
	Current Drawn:	150 +/- 10mA	
	Zero Offset:	0mV +/- 25mV	
	Sensitivity:	45 mV/%vol Acetylene	
	Range:	0-100% LEL	
	Linearity:	Effectively Linear to 50% LEL	
	Accuracy:	+/- 500ppm	
	Maximum Long Term Drift (Span):	< +/- 1% LEL/Month	
	Maximum Long Term Drift (Zero):	<+/- 0.5 mV/Month	
	Response Time:	T50: 3 sec T90: 8 sec	
Operating conditions	Operating Temperature:	20°C to + 70°C	
	Temperature Drift (Zero): (-20°C to +70°C)	< +/- 2% LEL	
	Operating Humidity:	0-195% RH, non-condensing	
	Humidity Response:	+/- 2% LEL	



Recommended circuit




Gas sensitivity






Temperature dependancy



Humidity dependancy





Relative response to various gases

Below is a table of NP-ACSMM responses to various flammable gases. The table assumes the sensor is measuring on the 0-100% LEL scale and assumes that the response to acetylene = 100%.

Note that the LEL data can be different in different countries. In Europe, the LEL's used are defined in the IEC standard IEC80079-20-1, whilst in the USA and various other areas, LELs are generally taken from the US Bureau of Mines Bulletin Document 627.

Technically, both are correct; the reason for the differences being that the measurements made for IEC80079-20-1 are with the gas in motion, whilst the US Bureau of Mines Bulletin Document 627 assumes the gas is not moving. For convenience, relative responses are given according to BOTH standards below.

Gas	Formula	LEL (Europe) (IEC80079-20-1)	Relative Response (%)	LEL (USA) (USBoM 627)	Relative Response (%)
Acetylene	C2H2	2.3	100	2.5	100
Acetone	(CH3)2CO	2.5	89	2.6	85
Ethanol	C2H5OH	3.1	92	3.3	90
Ethyl acetate	C2H5COOH	2	70	2.2	70
Ethylene	C2H4	2.3	88	2.7	95
Methane	CH4	4.4	0	5	0
Iso-butane	C4H10	1.3	28	1.8	35
Iso-propanol	СН3-С2Н4СООН	2	79	2.2	80
Methanol	СНЗОН	6	127	6.7	130
Methyl Ethyl Ketone	CH3(CO)C2H5	1.5	65	1.9	75
N-butane	C4H10	1.4	30	1.8	35
N-heptane	C7H16	0.85	53	1.05	60
N-hexane	C6H14	1	59	1.2	65
N-pentane	C5H12	1.1	47	1.4	55
Propane	C3H8	1.7	22	2.1	25
Toluene	C6H5CH3	1	64	1.2	70
Ammonia	NH3	15	180	15	165
Carbon monoxide	со	10.9	105	12.5	110
Hydrogen	H2	4	142	4	130
Unleaded Petrol				1.2	65



Warranty and warning

Use within specified conditions.

Sensor characteristics must be measured in clean air without noise gases.

Electrode pins must be correctly connected. Wrong connection does not allow correct functions.

Do not apply voltage directly to electrode pins.

Do not bend pins.

Do not solder to electrode pins directly. Use exclusive sockets.

Do not use contact grease on electrode pins.

Do not put excess strength on electrode pins.

If sensor housing is damaged or scratched, do not use sensor.

Do not blow organic solvents, paints, chemical agents, oils, or high concentration gases onto sensor.

Do not disassemble or change any parts.

If sensor is used under irregular atmosphere, contact us for assistance.

N.E.T. has a policy of continuous development and improvement of its products. As such the specification for the device outlined in the data sheet may be changed without notice. In case of modification of the product, N.E.T. disclaims all liability.

No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, including photocopying, recording, or other electronic or mechanical methods, without the prior written permission of N.E.T. For permission requests or technical support please contact or write to the address below:



N.E.T. SRL Via Legnano, 2 | 20010 | Cornaredo | Milano | Italy T +39.02.9354.4190 E info@nenvitech.com www.nenvitech.com

